



Part Number : [190070040](#)
Product Description : Flag InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm
Series Number : 19007
Status : Active
Product Category : Quick Disconnects
Engineering Number : C-2211



Documents & Resources

Drawings

[190070040_sd.pdf](#)

3D Models and Design Files

[190070040_stp.zip](#)

Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19007
Description	Flag InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753032149

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Gender	Female
Glow-Wire Capable	Yes
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.600/g
Orientation	Flag
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	6.65mm max.
Wire Size (AWG)	10 (105 strands), 12 (65 strands)

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for AviKrimp Fully Insulated and Insulated Quick Disconnect Flags, 12-10 AWG	<u>640018800</u>