



Part Number : 797582025

Product Description : Pre-Crimped Lead .062"
Male-to-.062" Male, Tin (Sn) Plating,
150.00mm Length, 22 AWG, Black

Series Number : 79758

Status : Active

Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings

797582025_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead .062" Male-to-.062" Male, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	.062" Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Standard .062"
UPC	889056822763

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Male-Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.647/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	22

Use with Part(s)

Description	Part Number
Standard .062" Pin and Socket Connector Housings	<u>1625</u>

