



**Part Number :** [2005280260](#)  
**Product Description :** Easy-On FFC/FPC Connector, 1.00mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 26 Circuits, Gold over Nickel Plating  
**Series Number :** 200528  
**Status :** Active  
**Product Category :** FFC / FPC Connectors



## Documents & Resources

**Drawings**  
[2005280260\\_sd.pdf](#)

**3D Models and Design Files**  
[2005280260\\_stp.zip](#)

**Specifications**  
[2005289200-200.pdf](#)  
[2005280000-PS-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
  - IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                                                                                                                         |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                  |
| Category     | FFC / FPC Connectors                                                                                                                    |
| Series       | 200528                                                                                                                                  |
| Description  | Easy-On FFC/FPC Connector, 1.00mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 26 Circuits, Gold over Nickel Plating |
| Series Name  | FD19                                                                                                                                    |
| Comments     | Black Actuator                                                                                                                          |
| Product Name | Easy-On                                                                                                                                 |
| UPC          | 191128825092                                                                                                                            |

#### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum             | 125V |

#### Physical

|                                |                        |
|--------------------------------|------------------------|
| Actuator Type                  | Front Flip             |
| Circuits (Loaded)              | 26                     |
| Circuits (maximum)             | 26                     |
| Color - Resin                  | Beige                  |
| Contact Position               | Bottom                 |
| Durability (mating cycles max) | 20                     |
| Mated Height                   | 1.90mm                 |
| Material - Metal               | Phosphor Bronze        |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Gold                   |
| Material - Resin               | Liquid Crystal Polymer |

|                               |                       |
|-------------------------------|-----------------------|
| Net Weight                    | 309.636/mg            |
| Orientation                   | Right Angle           |
| Packaging Type                | Embossed Tape on Reel |
| PCB Locator                   | No                    |
| PCB Mounting                  | Surface Mount         |
| PCB Retention                 | Yes                   |
| Pitch - Mating Interface      | 1.00mm                |
| Pitch - Termination Interface | 1.00mm                |
| Plating min - Mating          | 0.051µm               |
| Plating min - Termination     | 0.051µm               |
| Polarized to PCB              | Yes                   |
| Stackable                     | No                    |
| Temperature Range - Operating | -40° to +105°C        |
| Wire/Cable Type               | FFC/FPC               |

---

## Mates With / Use With

### Mates with Part(s)

| Description                         | Part Number  |
|-------------------------------------|--------------|
| 1.00mm Pitch Premo-Flex FFC Jumpers | <u>15039</u> |
| 1.00mm Pitch Premo-Flex FFC Jumper  | <u>15019</u> |