



Part Number : [357500910](#)
Product Description : Ring Tongue Terminal
for 18-14 AWG (0.75~2.08mm²), Stud Size 8
(M4), Tin Plating
Series Number : 35750
Status : Obsolete
Product Category : Ring and Spade Terminals



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
--------	----------

Category	Ring and Spade Terminals
Series	35750
Description	Ring Tongue Terminal for 18-14 AWG (0.75~2.08mm ²), Stud Size 8 (M4), Tin Plating
Keyword	Ring Terminal, Ring Terminals
Product Name	N/A
Type	Ring
UPC	800753199699

Agency

UL	E134962
----	---------

Electrical

Voltage - Maximum	300V AC
-------------------	---------

Physical

Barrel Type	Open
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.333/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Stud Size	8 (M4)
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.20mm max.
Wire Size (AWG)	14, 16, 18

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----