



Part Number : [190740021](#)
Product Description : Krimptite Steel Star Ring
Tongue Terminal for 16-14 AWG Wire, Stud
Size 6 (M3.5)
Series Number : 19074
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : SRB-S-129-06



Documents & Resources

Drawings
[190740021_sd.pdf](#)

3D Models and Design Files
[190740021_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Steel Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Type	Ring
UPC	800755072792

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.530/g
Packaging Type	Bag
Stud Size	6 (M3.5)
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640031200</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640071200</u>