



Part Number : [191640311](#)
Product Description : Perma-Seal Ring Tongue
Terminal for 16-14 AWG Wire, Stud Size 8
(M4), Mylar Tape Carrier
Series Number : 19164
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : SB-237-08T



Documents & Resources

Drawings
[191640311_sd.pdf](#)

3D Models and Design Files
[191640311_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19164
Description	Perma-Seal Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Perma-Seal
Type	Ring
UPC	800753115668

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	1.165/g
Packaging Type	Adhesive Tape on Reel
Stud Size	8 (M4)
Wire Insulation Diameter	5.97mm
Wire Size (AWG)	14, 16
Wire Size mm ²	1.23-1.94

Application Tooling

Global

Description	Part Number
ATP Perishable Tool Kit used in ATP Presses that Process Product on Tape	<u>198082012</u>
PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)	<u>640017400</u>
Power Crimp Tool Head for Terminals 22-10 AWG Wire	<u>640057400</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160041</u>

This document was generated on Feb 26, 2025