




Part Number : [5035661302](#)
Product Description : 0.30mm Pitch Easy-On FPC Connector, Right-Angle, Bottom Contact, 0.95mm Height, 13 Circuits, Gold over Nickel Plating
Series Number : 503566
Status : Active
Product Category : FFC / FPC Connectors



Documents & Resources

Drawings
[5035661302_sd.pdf](#)

3D Models and Design Files
[5035661302_stp.zip](#)

Specifications
[5035660000-A00.pdf](#)
[5035669200-200.pdf](#)
[5035660000-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	503566
Description	0.30mm Pitch Easy-On FPC Connector, Right-Angle, Bottom Contact, 0.95mm Height, 13 Circuits, Gold over Nickel Plating
Product Name	Easy-On
UPC	191128129756

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	10
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	22.752/mg
Orientation	Right Angle

Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only

Solder Process Data

Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	250

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.30mm Pitch Premo-Flex FPC Jumpers with Latching Ears	<u>15032</u>