




Part Number : [1731120735](#)
Product Description : FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 28-26 AWG, 5000 Pieces
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Number : FK20SL26-02V-6097



Documents & Resources

- Drawings**
[1731120735_sd.pdf](#)
- Specifications**
[1731120004-PK-000.pdf](#)
[2195600650-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 28-26 AWG, 5000 Pieces
Contact Type	Machined Crimp
Magnetic	Yes
Product Name	FCT Products
Type	Standard Density
UPC	191128856126

Electrical

Current - Maximum per Contact	7.5A
-------------------------------	------

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Net Weight	0.100/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.200µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp

Wire Size (AWG)	26, 28
-----------------	--------

Use with Part(s)

Description	Part Number
Use With	FCT Standard-Density Connectors

Application Tooling

Global

Description	Part Number
FCT Hand Crimp Tool, Mini Frame, 8-Step Adjust	<u>1731121730</u>
FCT Installation and Removal Tool for D-Subs	<u>1731121744</u>
FCT Locator for Size 20 Contacts, Socket	<u>1731121763</u>