



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





KIT

REPRESENTATION ONLY

TE Part # 7-2150065-7

[OCEAN_2.0_SPARE_PART_KIT-110F](#)




TE

TE Part # 2150065-2

[OCEAN_2.0_Applicator-E-110F-SEA](#)

Customers Also Bought



TE

TE Part #62000-1


[SPLICE AMVAR 600-3000 020BR](#)



TE

TE Part #61-0022-011-000

[CONTACT PIN 2 MM](#)



TE

TE Part #87165-1


[LOCKING CLIP ASSY .025 SQ LP](#)



TE

TE Part #CKA267M39440051000

[940 EXTENSION, SPEEDTEC-READY](#)



TE

TE Part #926657-4

[LOCKING CLIP HSG](#)



TE

TE Part #927840-5

[SPT REC 6.3 Contact SRC Ag](#)



TE

TE Part #BKA186M21480200000

[923 EXTENSION, SPEEDTEC-READY](#)



TE

TE Part #8B-0067-001-000

[617/917 METAL PROTECTION CAP FOR PLUG](#)

Documents

Product Drawings

AMPLIVAR SPLICE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_280005-1_S.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280005-1_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280005-1_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Magnet Wire Terminals & Splices

English

Product Specifications

Application Specification

English

AMPLIVAR 7 Serration Pigtail Splice

English