

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

DYMO® XTL™ Marking Kit



General description:

- Cable and component marking
- Indoor and outdoor marking
- DYMO® XTL™ marking kit with industrial label maker XTL™ 500

Delivery:

DYMO® XTL™ marking kit is delivered in a bag with label marker, marking tape, batteries, charger and quick guide.

Other product data:

ETIM Classification: EC001288

Advantages:

- Marking in one bag for both cables and components
- Can be used both for indoor and outdoor marking
- Time-saving features to simplify labelling
- On screen print preview and colour display
- Built-in label applications make getting started easy
- Pre-loaded label templates ensure perfect formatting to save time
- Many different industrial label types available

Related products:

For the DYMO® XTL™ Marking kit there are many different labels available in the assortment, such as multifunctional vinyl, permanent polyester, shrink tube, laminated cable label and preformatted labels.

Storage:

Cool and dry in original packaging.

Technical data Marking kit with XTL™ 500:

"Printing system XTL 500: Heat transfer
Maximum label width: 54mm
Label type: DYMO XTL
Screen size: 109.22 mm colour

Document: DB83257106EN

Version: 03

We reserve all rights according to DIN ISO 16016.
PD 0019/05_04.18EN



83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

Print speed: 28 mm/s
 Keyboard: QWERTY
 Resolution: 300 dpi
 Printable rows: 24
 Barcodes: Code 128 (Auto), Code 39, code 39 Mod, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code
 Knife: Automatic
 Memory: 41MB
 PC connection: Yes
 Software: DYMO ID (free of charge, downloadable)
 Compability: Windows 7 and later

Product data Marking kit XTL™ 500:

Art. no.	Article type	Packaging unit	Unit
83257107	DYMO® XTL Kit 500 54	1	1
Accessories			
83257221	DYMO® XTL 500 AC ADAPTER	1	1
83257222	DYMO® XTL 500 Cutter	1	1
83257223	DYMO® XTL 500 Li-14.8V Battery	1	1

DYMO® XTL™ MARKING TAPE



General description:

- Industrial labels for tough environments
- Many different label types available
- Suits DYMO® XTL™ 300 Label printer or DYMO® XTL™ 500

Delivery:

DYMO® XTL™ Marking tapes are delivered separately.

Other product data:

ETIM Classification: EC001288

Advantages:

- Many different industrial label types available
- High resistance towards moisture, UV, chemicals and much more
- Applicable on many different usage areas
- UL969 approval (Standard for Marking and Labelling Systems)

Document: DB83257106EN Version: 03	Page 2 of 7
---------------------------------------	-------------

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

Related products:

Suits DYMO® XTL™ 300 Label printer or DYMO® XTL™ 500.

Storage

Cool and dry in original packaging.

DYMO® XTL™ INDUSTRIAL MARKING TAPE

Advantages industrial marking tape:

- Pre-defined industrial labels for XTL label printers
- Ideal marking for flat surfaces
- Easier printing of label series
- UL recognised as a component to UL969

Technical data industrial marking tape:

Material: Vinyl

Temperature area: -40°C to +60°C

Mounting surface: Flat and structured

Usage: Indoor and outdoor

Resistance: UV, moisture

UL Approval: UL969, RoHS



Product data industrial marking tape:

Art. no.	Article type	Colour	Size (mm)	Packaging unit	Unit
83257110	DYMO® XTL Label 12x12WH	White	12x12	250	1
83257111	DYMO® XTL Label12x25WH	White	12x25	250	1
83257112	DYMO® XTL Label12x38WH	White	12x38	185	1
83257113	DYMO® XTL Label 25x25WH	White	25x25	250	1
83257114	DYMO® XTL Label 9x25WH	White	9x25	250	1
83257115	DYMO® XTL Label 12x19WH	White	12x19	250	1
83257116	DYMO® XTL Label 19x25WH	White	19x25	250	1
83257117	DYMO® XTL Label 25x51WH	White	25x51	100	1
83257118	DYMO® XTL Label 51x76WH	White	51x76	100	1

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

DYMO® XTL™ PRE-FORMATED MARKING TAPE

Advantages Pre-formatted marking tape:

- Industrial pre-sized safety labels
- Coloured headers included according to OSHA, ANSI och ISO colour standards
- Ideal marking for flat surfaces
- UL recognised as a component to UL969

Technical data Pre-formatted marking tape:

Material: Vinyl

Temperature range: -40°C till +60°C

Mounting: flat and structured surface

Usage: Indoor and outdoor

Resistance: UV, moisture

UL Approval: UL969, RoHS

Colour standard: OSHA, ANSI, ISO

Product data Pre-formatted marking tape:

Art. no.	Article type	Colour	Header text	Size (mm)	Packaging unit	Unit
83257128	DYMO® XTL Label 51x102OG&WH	Orange & White	-	51x102	70	1
83257129	DYMO® XTL Label 51x102YE&WH	Yellow & White	-	51x102	70	1
83257130	DYMO® XTL Label 51x102BU&WH	Blue & White	NOTICE	51x102	70	1
83257131	DYMO® XTL Label 51x102RD&WH	Red & White	DANGER	51x102	70	1

DYMO® XTL™ SHRINK TUBE MARKING

Advantages Shrink tube marking:

- Industrial shrink tube
- Shrink ratio 3:1 ensures a secure fit on cables
- UL recognized as a component to UL969

Technical data Shrink tube marking:

Material: Polyolefin

Temperature range: Maximum +125°C

Mounting: round surface

Shrink ratio: 3:1

Usage: Indoor

Resistance: UV, oil, moisture, chemicals

UL Approval: UL224, RoHS

MIL-spec & SAE: MIL-M-8153, MIL-STD-202G, SAE-DTL-230535 (class 1 & 3)

Product data Shrink tube marking:

Art. no.	Article type	Colour	Size (mm)	Packaging unit	Unit
83257134	DYMO® XTL Heat-Shrink 24x34WH	White	24x34	60	1
83257138	DYMO® XTL Heat-Shrink 24x47WH	White	24x47	60	1
Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257214	DYMO® XTL Heat-Shrink 6BK/WH	White	2.7 m	1	1
83257215	DYMO® XTL Heat-Shrink 12BK/WH	White	2.7 m	1	1
83257216	DYMO® XTL Heat-Shrink 24BK/WH	White	2.7 m	1	1

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

DYMO® XTL™ FLAT MARKING TAPE

Advantages Flat marking tape:

- Industrial label for flat surfaces
- Marking of panels etc.
- Transparent blank surface on label for professional appearance
- UL identified as component to UL969

Technical data Flat marking tape:

Material: Polyester

Temperature range: -40°C to +60°C

Mounting: flat and structured surfaces

Usage: Indoor and outdoor

Resistance: UV, oil, moisture, chemicals

UL Approval: UL969, RoHS

Colour standard: OSHA, ANSI, ISO

Product data Flat marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257140	DYMO® XTL Label Flat 6WH	White	9.1	1	1
83257141	DYMO® XTL Label Flat 9WH	White	9.1	1	1
83257142	DYMO® XTL Label Flat 12WH	White	9.1	1	1
83257143	DYMO® XTL Label Flat 6TR	Transparent	9.1	1	1
83257144	DYMO® XTL Label Flat 9TR	Transparent	9.1	1	1
83257145	DYMO® XTL Label Flat 12TR	Transparent	9.1	1	1

DYMO® XTL™ CABLE MARKING TAPE

Advantages Cable marking tape:

- Industrial label with flexible cable wraps
- Ideal for marking wires, cables and round surfaces
- Tear proof material
- Resistance towards damage when pulled through tight spaces and conduits
- UL recognized as a component to UL968

Technical data Cable marking tape:

Material: Nylon

Temperature range: -40°C to +80°C

Mounting: round surface

Usage: Indoor

Resistance: UV, oil, moisture, chemicals

UL Approval: UL969, RoHS

Product data Cable marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257211	DYMO® XTL Cable wrap 12BK/WH	White	5.5	1	1
83257212	DYMO® XTL Cable wrap 19BK/WH	White	5.5	1	1
83257213	DYMO® XTL Cable wrap 24BK/WH	White	5.5	1	1

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

DYMO® XTL™ Vinyl MARKING TAPE

Advantages Vinyl marking tape:

- Industrial multi-function vinyl label
- Ideal for indoor and outdoor marking
- Resistance towards moisture, chemical and UV
- Wide range of colours to fit with OSHA, ANSI and ISO colour standards and workplace communication and safety
- UL recognised as a component to UL969

Technical data Vinyl marking tape:

Material: Vinyl

Temperature range: -40°C to +60°C

Mounting: flat, round and structured surface, flag label

Usage: Indoor and outdoor

Resistance: UV, oil, moisture, chemicals

UL Approval: UL969, RoHS

Colour standard: OSHA, ANSI, ISO

Product data Vinyl marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257146	DYMO® XTL Label VIN 12BK/TR	Transparent	7	1	1
83257148	DYMO® XTL Label VIN 24BK/TR	Transparent	7	1	1
83257149	DYMO® XTL Label VIN 41BK/TR	Transparent	7	1	1
83257151	DYMO® XTL Label VIN 12RD/TR	Transparent	7	1	1
83257152	DYMO® XTL Label VIN 19RD/TR	Transparent	7	1	1
83257153	DYMO® XTL Label VIN 24RD/TR	Transparent	7	1	1
83257154	DYMO® XTL Label VIN 41RD/TR	Transparent	7	1	1
83257155	DYMO® XTL Label VIN 54RD/TR	Transparent	7	1	1
83257156	DYMO® XTL Label VIN 12BK/WH	White	7	1	1
83257157	DYMO® XTL Label VIN 19BK/WH	White	7	1	1
83257158	DYMO® XTL Label VIN 24BK/WH	White	7	1	1
83257159	DYMO® XTL Label VIN 41BK/WH	White	7	1	1
83257160	DYMO® XTL Label VIN 54BK/WH	White	7	1	1
83257161	DYMO® XTL Label VIN 12RD/WH	White	7	1	1
83257162	DYMO® XTL Label VIN 19RD/WH	White	7	1	1
83257163	DYMO® XTL Label VIN 24RD/WH	White	7	1	1
83257164	DYMO® XTL Label VIN 41RD/WH	White	7	1	1
83257165	DYMO® XTL Label VIN 54RD/WH	White	7	1	1
83257168	DYMO® XTL Label VIN 24WH/RD	Red	7	1	1
83257169	DYMO® XTL Label VIN 41WH/RD	Red	7	1	1
83257170	DYMO® XTL Label VIN 54WH/RD	Red	7	1	1
83257171	DYMO® XTL Label VIN 12BK/OG	Orange	7	1	1
83257172	DYMO® XTL Label VIN 19BK/OG	Orange	7	1	1
83257173	DYMO® XTL Label VIN 24BK/OG	Orange	7	1	1
83257174	DYMO® XTL Label VIN 41BK/OG	Orange	7	1	1
83257175	DYMO® XTL Label VIN 54BK/OG	Orange	7	1	1
83257176	DYMO® XTL Label VIN 12BK/YE	Yellow	7	1	1
83257178	DYMO® XTL Label VIN 24BK/YE	Yellow	7	1	1
83257179	DYMO® XTL Label VIN 41BK/YE	Yellow	7	1	1
83257180	DYMO® XTL Label VIN 54BK/YE	Yellow	7	1	1

83257106	DATA SHEET
Valid from: 08.11.2021	DYMO® XTL™ MARKING KIT & MARKING TAPE

Product data Vinyl marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257181	DYMO® XTL Label VIN 12WH/BU	Blue	7	1	1
83257182	DYMO® XTL Label VIN 19WH/BU	Blue	7	1	1
83257183	DYMO® XTL Label VIN 24WH/BU	Blue	7	1	1
83257184	DYMO® XTL Label VIN 41WH/BU	Blue	7	1	1
83257185	DYMO® XTL Label VIN 54WH/BU	Blue	7	1	1
83257186	DYMO® XTL Label VIN 12WH/GN	Green	7	1	1
83257187	DYMO® XTL Label VIN 19WH/GN	Green	7	1	1
83257188	DYMO® XTL Label VIN 24WH/GN	Green	7	1	1
83257189	DYMO® XTL Label VIN 41WH/GN	Green	7	1	1
83257190	DYMO® XTL Label VIN 54WH/GN	Green	7	1	1
83257191	DYMO® XTL Label VIN 12WH/BN	Brown	7	1	1
83257192	DYMO® XTL Label VIN 19WH/BN	Brown	7	1	1
83257193	DYMO® XTL Label VIN 24WH/BN	Brown	7	1	1
83257194	DYMO® XTL Label VIN 41WH/BN	Brown	7	1	1
83257195	DYMO® XTL Label VIN 54WH/BN	Brown	7	1	1
83257196	DYMO® XTL Label VIN 12WH/VT	Violet	7	1	1
83257197	DYMO® XTL Label VIN 19WH/VT	Violet	7	1	1
83257198	DYMO® XTL Label VIN 24WH/VT	Violet	7	1	1
83257199	DYMO® XTL Label VIN 41WH/VT	Violet	7	1	1
83257200	DYMO® XTL Label VIN 54WH/VT	Violet	7	1	1
83257201	DYMO® XTL Label VIN 12WH/BK	Black	7	1	1
83257202	DYMO® XTL Label VIN 19WH/BK	Black	7	1	1
83257203	DYMO® XTL Label VIN 24WH/BK	Black	7	1	1
83257204	DYMO® XTL Label VIN 41WH/BK	Black	7	1	1
83257205	DYMO® XTL Label VIN 54WH/BK	Black	7	1	1
83257206	DYMO® XTL Label VIN 12BK/GY	Grey	7	1	1
83257207	DYMO® XTL Label VIN 19BK/GY	Grey	7	1	1
83257208	DYMO® XTL Label VIN 24BK/GY	Grey	7	1	1
83257209	DYMO® XTL Label VIN 41BK/GY	Grey	7	1	1
83257210	DYMO® XTL Label VIN 54BK/GY	Grey	7	1	1

Foot note:

Photographs are not to scale and do not represent detailed images of the respective products.

Document: DB83257106EN Version: 03	Page 7 of 7
---------------------------------------	-------------