

61814612	DATA SHEET	
Valid from: 08.02.2023	TWISTOR®	

The TWISTOR® crimping tool are for crimping insulated and non-insulated ferrules acc. To DIN 46228.
The crimping tool automatically adjust to the desired crimping cross-section and has always the same results thanks to the completion system.
The TWISTOR® crimping tool combines the properties from Front- and Side crimping in one universal tool.

Technical features:

Crimp insert	360° rotatable
Material	Chrome
Scope of Application	insulated and non-insulated Ferrules acc to DIN 46228
Cross-section	0,14 up to 16mm ² / AWG 26 - 6
TWIN-Ferrule	2x0,25 up to 10mm ² / AWG 28 - 8



TWISTOR® 16



TWISTOR® T

Part No.	Part Description	For mm ²	TWIN-Ferrule	Crimp profile
6181 4612	CRIMPWERKZEUG PEW 8.190 TWISTOR 16	0,14 bis 16 mm ² AWG 26 - 6	2x0,25 – 6 mm ² 2x AWG 28 - 8	Square
6181 4613	CRIMPWERKZEUG PEW 8.191 TWISTOR T	0,14 bis 10 mm ² AWG 26 - 8	2x0,25 – 6 mm ² 2x AWG 22 - 8	Trapeze

Creator: MAAU1/PDP Released: DAMU1/PDP	Document: DB6 18 146 12EN Version: 00	Page 1 of 1
---	--	-------------