

11148004	DATA SHEET	
Valid from: 19.06.2024	EPIC® CRIMPTOOL D-SUB	

Description

- Crimptool for D-Sub contacts



Article Number	Article	Description	Version	For design
Crimping tool				
11148004	D-Sub crimping tool	Digital crimp tool for D-Sub contacts	0,08 - 2,50mm ²	MH Gigabit M23 D-Sub MC 20 Pol
11148302	D-Sub Locator	Locator for D-Sub crimpcontacts	0,08 - 2,50mm ²	MH Gigabit M23 D-Sub MC 20 Pol

Crimpeinstellungen

Article Number	Cross section [mm ²]	Crimping tool adjustment	Locator position
44423356 EPIC® Signal D-Sub BCM 1 mm	0,25	1,00	4
	0,34	1,05	
	0,50	1,10	
	0,75	1,15	
	1,00	1,20	
44423357 EPIC® Signal D-Sub SCM 1 mm	0,25	1,00	3
	0,34	1,05	
	0,50	1,10	
	0,75	1,15	
	1,00	1,20	

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

The digital display is operated with a CR2025 button cell

Creator: STKU3/PDP Released: IVSE1/PDP	Document: DB11148004EN Version: 00	Page 1 of 1
---	---------------------------------------	-------------

We reserve all rights according to DIN ISO 16016.

PD 0019/05_04.18EN