

6172 1260	DATA SHEET	
Valid from: 06.03.2019	SILVYN® BRAID PA6	

SILVYN® BRAID PA6 is a polyamide braided sleeve with a special coating, the coat enable that the braided sleeve can cut by a normal scissor (cold cut) without frizzle. The sleeve is abrasion-resistant, protects before dust and is resistant against chemical fluids. The SILVYN® BRAID PA6 can be used as a simple cable protection, additional insulation, bonding and guiding of cables and wires und low rodent protection.



Material:

Polyamide 6.6

Technical features:

Profile

Braided sleeve

Nominal size

NW 6 up to NW 40

Temperature range

-55°C up to +125°C

Additional features:

Fire classification

V2 acc. to UL94

Flammability

Self-extinguishing acc. to FMVSS 302

Free of halogen und cadmium

UV-Resistant

Color:

Black



Approbation:

Dimension table:

Part No.	Nominal width NW	Scope of Application mm		VPE m
		Smallest Diameter	Largest Diameter	
6172 1260	6	4,0	10,0	20
6172 1266				750
6172 1261	12	10,0	14,0	15
6172 1267				500
6172 1262	16	14,0	24,0	15
6172 1268				400
6172 1263	20	18,0	26,0	10
6172 1269				250
6172 1264	30	26,0	36,0	10
6172 1258				250
6172 1265	40	32,0	44,0	5
6172 1259				250

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: MAU1/PDP Released: DAMU1/PDP	Document: DB61721260EN Version: 03	Page 1 of 1
--	---------------------------------------	-------------