

6172 1270	DATA SHEET	
Valid from: 08.05.2018	SILVYN® SHRINK BRAID PET	

SILVYN® SHRINK BRAID PET consists of PET protective fibres and has a highly Abrasion-resistant and very good shrink results, also in small radius. The shrinkable braided hose offers protection against dust and liquids, abrasion protection and flexibility. Applicable for easy cable protection, additional insulation, bundling and guiding of cables and wires.



Material: PET

Technical features:

Profile	Shrinkable woven braid
Nominal size	NW 6 up to NW 70
Temperature range	-40°C up to +150°C
Processing temperature	+180°C up to +220°C
Shrink ratio	2:1

Additional features:

Fire classification	HB acc. to UL94
Free of halogen und cadmium	

Color: Black



Approbation:

Dimension table:

Part No.	Nominal width NW	Shrinkable range mm		Wall Thickness mm
		Smallest Diameter	Largest Diameter	
6172 1270	6 – 12	6	12	0,7
6172 1271	12 – 25	12	25	0,7
6172 1272	15 – 30	15	30	0,7
6172 1273	25 – 50	25	50	0,7
6172 1274	35 – 70	35	70	0,7

Creator: MAAU1/PDP Released: DAMU1/PDP	Document: DB61721270EN Version: 02	Page 1 of 1
---	---------------------------------------	-------------