

10027710	DATA SHEET	
Valid from: 17.09.2018	EPIC® H-B 24 Q+E MOUNTING SYSTEM TOP PART	

Description

- For mounting inserts on top-hat rails according to DIN EN 60715



General Characteristics

Configuration	Top part
Version	H-B 24
Temperature Range	-40°C to +100°C, short-term up to +125°C

Mechanical Characteristics

Cycle of mechanical operation	max. 50
-------------------------------	---------


Materials and Surfaces

Material	PC
Flammability Class according to UL 94	V0

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB10027710EN Version: 01	Page 1 of 2
---	---------------------------------------	-------------

10027710	DATA SHEET	
Valid from: 17.09.2018	EPIC® H-B 24 Q+E MOUNTING SYSTEM TOP PART	

Drawings



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB10027710EN Version: 01	Page 2 of 2
---	---------------------------------------	-------------