

61810350	DATA SHEET
Valid from: 18.01.2024	TY-FAST® Cable Tie

One part plastic cable tie for bundling and fixing from cables.

Material:

Polyamide 6.6

Technical Features:

Bundle diameter

1,5 up to 102mm

Bandwidth

2,5 up to 7,6mm

Tensile strength

80 up to 550N

Temperature range

Natural -40°C up to +85°C

Black -40°C up to +115°C

Installations temperature

-10°C



Additional features:

Fire Classification

V2 acc. to UL 94

UV-Resistant

only Black

Color:

Black

Natural

Norm Reference:



Dimensions:

Part No.	Bundle diameter mm		Size mm		Tensile strength N
	min.	max.	Length	Wide	
TY-FAST® Natural					
61810350	1,5	20,5	100	2,5	80
61810360	1,5	36,5	150	2,5	80
61810370	1,5	52,5	200	2,5	80
61810380	1,5	32	143	3,6	180
61810390	2,0	52,5	203	3,6	180
61810400	6,4	76	290	3,6	180
61810410	3,2	44	188	4,7	222
61810420	3,2	76	3,4	4,7	222
61810430	3,2	102	366	4,7	222
61810440	6,0	56	220	7,6	550
61810450	15	102	374	7,6	540
TY-FAST® Black					
61810460	1,5	20,5	100	2,5	80
61810470	1,5	36,5	150	2,5	80
61810480	1,5	52,5	200	2,5	80
61810490	1,5	32	143	3,6	180
61810500	2,0	52,5	203	3,6	180
61810510	6,4	76	290	3,6	180
61810520	3,2	44	188	4,7	222

61810350	DATA SHEET
Valid from: 18.01.2024	TY-FAST® Cable Tie

61810530	3,2	76	3,4	4,7	222
61810540	3,2	102	366	4,7	222
61810550	6,0	56	220	7,6	550
61810560	15	102	374	7,6	540