VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

UC-4C1A240W01
USB CHARGING STATION WITH DISPLAY 240 W

CE

Item no: 3374356



The product is a 4x USB-C® and 1x USB-A GaN (gallium nitride) charger with support for PD (power delivery) fast charging.
The product has a display that indicates real-time output for connected devices.

TECHNICAL DATA

General

Charging ports	4x USB-C®: Power delivery (PD 3.0) 1x USB-A: Super fast charging
Charger type	GaN

Data according to EU regulation 2019/1782

Manufacturer	Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau
Commercial registration number	HRB 3896
Model identifier	UC-4C1A240W01
Input voltage	200 - 240 V/AC
Input AC frequency	50/60 Hz
Output voltage Output current Output power	**USB-C1** Output: 5V-20V/DC 5A or 5V/DC 3A or 9V/DC 3A or 12V/DC 3A or 15V/DC 3A or 20V/DC 5A or 28V/DC 5A (140W Max) **USB-C2/C3** Output: 3.3V-21V/DC 5A or 5V/DC 3A or 9V/DC 3A or 12V/DC 3A or 15V/DC 3A or 20V/DC 5A (100W Max)

	USB-C4 Output: 3.3V-11V/DC 5A or 5V/DC 3A or 9V/DC 3A or 12V/DC 3A or 15V/DC 3A or 20V/DC 3.25A (65W Max) **USB-A** Output: 5V/DC 3A or 9V/DC 3A or 10V/DC 2.25A or 12V/DC 2.5A or 20V/DC 1.5A (30 W Max) **USB-C1+USB-C2 or USB-C1+USB-C3** Output: 140W + 100W **USB-C4+USB-A** Output: 5V/DC 1.5A+5V/DC 1.5A **USB-C1+USB-C2 + USB-C3 or USB-C4** Output: 100W + 65W + 65W **USB-C1+USB-C2 + USB-A** Output: 100W + 65W + 18W **USB-C1+USB-C2 + USB-C3+USB-C4** Output: 100W + 65W + 45W + 30W **USB-C1+USB-C2+USB-C3+(USB-C4+USB-A)** Output: 100W + 65W + 45W + (5V/DC 3A) Total Output: 240W (Max)
Average active efficiency	88.0 %
Efficiency at low load (10 %)	77.9 %
No-load power consumption	0.29 W

Environment

Operating temperature	0 to +40 °C
Operating humidity	5 - 90 % RH (non-condensing)
Storage temperature	-35 to +70 °C
Storage humidity	0 - 90 % RH (non-condensing)

Others

Dimensions (W x H x D) (approx.)	120 x 86.7 x 36.5 mm
Weight (approx.)	525 g (with power cord)

CONTENTS

Product // Power cord (2 m) // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3374356_V1_0926_en_ds 9007202554728843 I2/O1 en