



ICY BOX IB-DK2106a-CPD

USB Type-C® Docking Station with triple video output

Key features

- Premium aluminium enclosure
- USB Type-C® with Power Delivery
- Charge your notebook with up to 100 W via the USB Type-C® interface
- Three additional video interfaces:
2x High Speed HDMI® Type-A (up to 3840x2160@60 Hz)
1x VGA interface up to 1920x1200@60 Hz
- Three USB 3.0 Type-A interfaces, data transfer rate up to 5 Gbit/s
- Single LUN SD 3.0 (UHS-I) and microSD 3.0 (UHS-I) card reader for data transfer up to 100 MB/s
- Gigabit LAN RJ45 interface with wake-on-LAN function
- 3.5 mm stereo combo jack (headset)



Packing content

1x IB-DK2106a-CPD, 1x manual

Unlimited flexibility!

HDMI® is extremely common, that is why, our new DockingStation is equipped with two of those, along side with the classic VGA. As to the positioning and alignment, right, left, back or forth, does not matter anymore, since top and bottom play no role and thanks to the longer nylon coated cable, the setup can now be arranged without restrictions – as said... Universal!

Technical data

Model	IB-DK2106a-CPD
Article no.	61145
EAN	4250078174790
Brand	ICY BOX
Colour	Anthracite / black
Material	Aluminium + plastic
Input interface	USB Type-C® to host computer, integrated cable, 50 cm
Output interface	2x High Speed HDMI® 1x VGA 3x USB 3.0 Type-A, 2x 5 V@0.9 A, 1x 5 V@1.5 A 1x Gigabit LAN RJ45 interface 1x 3.5 mm stereo combo jack (microphone in / audio out) 1x SD & microSD card reader, SD 3.0 (UHS-I), Single LUN 1x Type-C® charging port for Power Delivery up to 100 W (20 V@5 A), no data transfer

Video resolution

High Speed HDMI® up to 1x 3840x2160@60 Hz
VGA up to 1920x1200@60 Hz

Data transfer rate

USB 3.0: up to 5 Gbit/s, UASP supported
LAN: up to 10/100/1000 Mbit/s

Power supply

Bus powered

Power Delivery

Supports up to 100 W from original power supply of the computer
Windows® 10

Operating system

USB Type-C® enabled Windows®.

System requirements

DisplayPort® Alt Mode and Power Delivery support required!
The device is compatible with Thunderbolt® 3 equipped computers
Dual video output: HDMI® + HDMI® or HDMI® + VGA synchronous display. No power supply included (only necessary for Power Delivery)



ICY BOX **IB-DK2106a-CPD** USB Type-C® DockingStation with triple video output



More Options

Docking Stations not only offer users a way to quickly transition from one working environment to another via a single cable, they can also add additional functionality and capabilities to notebook designs that are increasingly slim and with limited interface option.



USB Type-C®

The Type-C® connection offers incredible versatility. It combines data transmission, video output and power in a single, compact port. The integration of USB Type-C® makes the connection even more practical, as it has a twist-proof connection as its physical feature - making it a truly universal connection.



Easy connection - multiple benefits

Perfectly combines high-quality appearance and efficient technology with a very compact size. The premium aluminium Docking Station does not only look good but also offers high comfort while using. This solution is suited for any location such as private or office areas.

Logistical data

Packing unit: 20 pcs./carton
Total weight: 9.60 kg/carton
Gross weight (with packing): 0.420 kg
Net weight: 0.290 kg

Dimension/carton: 365x285x305 mm
Dimension (with packing): 340x130x30 mm
Dimension of article: 75x277x17 mm
Country of origin: China