



Part Number : [1212010015](#)
Product Description : mPm DIN Valve Connector, Form A-18mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Gray, Nitrile Gasket, Unmounted, Single Pack
Series Number : 121201
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : C28300G0R



Documents & Resources

Drawings
[1212010015_sd.pdf](#)

Specifications
[PS-121201-001-001.pdf](#)
[STR-1251-001.pdf](#)
[TS-121201-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per ED/71/2019 (16 July 2019)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121201
Description	mPm DIN Valve Connector, Form A-18mm, External Thread, 3 Pole Plus Ground Terminal, 250V AC/DC, Gray, Nitrile Gasket, Unmounted, Single Pack
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906916169

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Form	A - 18mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A

Material - Plating Mating	Silver
Net Weight	22.541/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	3
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A