



Part Number : [2210503466](#)
Product Description : mPm DIN Valve Connector, Form A - 18mm 2 Pole to 5.0m Black PUR UL Cable Pigtail, Yellow LED, Black Integrated Gasket, 24V
Series Number : 221050
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : E452B3A5001PS0H



Documents & Resources

Drawings
[2210503466_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 7(c)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	221050
Description	mPm DIN Valve Connector, Form A - 18mm 2 Pole to 5.0m Black PUR UL Cable Pigtail, Yellow LED, Black Integrated Gasket, 24V
IP Rating	IP67
Product Name	mPm
Protocol	EtherNet
Type	Single Ended
UPC	78172529121

Agency

UL	E218123
----	---------

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	24V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene

Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	N/A
Net Weight	351.200/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	PUR
Wire Size (AWG)	18

This document was generated on Feb 26, 2025