



Part Number : [1212010034](#)
Product Description : mPm DIN Valve Connector, Form A-18mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Nitrile Gasket, Mounted, Bulk Pack
Series Number : 121201
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : C28200N2RSN



Documents & Resources

Drawings
[1212010034_sd.pdf](#)

Specifications
[STR-1251-001.pdf](#)
[TS-121201-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121201
Description	mPm DIN Valve Connector, Form A-18mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Nitrile Gasket, Mounted, Bulk Pack
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982247994

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

Physical

Cable Diameter	4.00-9.00mm (.157-.354")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Form	A - 18mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A

Material - Plating Mating	Silver
Net Weight	18.320/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	16