



Part Number : [2210509005](#)
Product Description : mPm DIN Valve Connector, Form B - 11mm 2 Pole to 3.0m Black WSOR UL Cable Pigtail, Yellow LED + VDR, Black Profile Nitrile Gasket, 24V
Series Number : 221050
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : E462W3A30021C4H



Documents & Resources

Drawings
[2210509005_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	221050
Description	mPm DIN Valve Connector, Form B - 11mm 2 Pole to 3.0m Black WSOR UL Cable Pigtail, Yellow LED + VDR, Black Profile Nitrile Gasket, 24V
IP Rating	IP65
Product Name	mPm
Protocol	EtherNet
Type	Single Ended
UPC	889056669313

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	24V

Physical

Cable Diameter	6.40mm (.252")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	WSOR TPU
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A

Material - Plating Mating	N/A
Net Weight	198.000/g
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	18

This document was generated on Feb 26, 2025