



Part Number : [192020056](#)

Product Description : NylaKrimp Butt Splice
for 4 AWG Wire

Series Number : 19202

Status : Active

Product Category : Splices

Engineering Number : F-764



Documents & Resources

Drawings

[192020056_sd.pdf](#)

3D Models and Design Files

[192020056_stp.zip](#)

Specifications

[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19202
Description	NylaKrimp Butt Splice for 4 AWG Wire
Product Name	Butt,NylaKrimp
UPC	800753048348

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed - Brazed
Color - Resin	Yellow
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	16.343/g
Packaging Type	Bag
Temperature Range - Operating	-55° to +105°C

Wire Insulation Diameter	10.92mm max.
Wire Size (AWG)	4

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890007</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for 4 AWG Insulated Ring Terminals	<u>640017870</u>