



Part Number : 2153111041
Product Description : Mizu-P25 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Waterproof, Single Row, 150.00mm Length, Tin (Sn) Plating, 4 Circuits, Black
Series Number : 215311
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
2153111041_sd.pdf

3D Models and Design Files
2153111041_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215311
Description	Mizu-P25 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Waterproof, Single Row, 150.00mm Length, Tin (Sn) Plating, 4 Circuits, Black
Application	Signal, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mizu-P25-to-Pigtail
Product Name	Mizu-P25 Waterproof
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264682546

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V

Physical

Cable Length	150.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	5.591/g

Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	PVC
Wire Insulation Diameter	1.40-1.90mm
Wire Size (AWG)	20, 22

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mizu-P25 Waterproof Plug Housings	<u>52266</u>