



Part Number : [191640057](#)
Product Description : Perma-Seal Butt Splice
for 12-10 AWG Wire, Mylar Tape Carrier
Series Number : 19164
Status : Active
Product Category : Splices
Engineering Number : SC-12-10T



Documents & Resources

Drawings

[191640057_sd.pdf](#)

3D Models and Design Files

[191640057_stp.zip](#)

Specifications

[PS-19902-011-001.pdf](#)

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19164
Description	Perma-Seal Butt Splice for 12-10 AWG Wire, Mylar Tape Carrier
Product Name	Butt - Funnel Entry,Perma-Seal
UPC	800753113428

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.422/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	7.87mm max.

Wire Size (AWG)	10, 12
-----------------	--------

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880279</u>
PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)	<u>640017400</u>
Power Crimp Tool Head for Terminals 22-10 AWG Wire	<u>640057400</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160041</u>