

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0398600402

Status:

Obsolete

Description:

5.08mm (.200") Pitch Beau™ Eurostyle™ Vertical PCB Header, Open Ends Stackable, 2 Circuits

Replacement Part Number:

39531-0002

Documents:

[Drawing \(PDF\)](#)

Agency Certification

CSA	LR25562
UL	E48521

General

Product Family	Terminal Blocks
Series	39860
Application	Wire-to-Board
Comments	Gold plating available Other housing colors available
Component Type	PCB Header
Product Name	Eurostyle™ Pluggable
Replacement Part Number	39531-0002
Type	Euro Block

Physical

Circuits (Loaded)	2
Color - Resin	Black
Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PC Tail Length	4.32mm (.170")
PCB Retention	N/A
Panel Mount	No
Pitch - Mating Interface	5.08mm (.200")
Pitch - Termination Interface	5.08mm (.200")
Plating min - Mating	3.810µm (150µ")
Plating min - Termination	3.810µm (150µ")
Polarized to Mating Part	Yes
Shrouded	Open Ends
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	15A
Voltage - Maximum	300V

Solder Process Data

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

Material Info

Old Part Number	861502
-----------------	--------

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39860Series

Mates With

39860 Plugs

Reference - Drawing Numbers

Sales Drawing

SD-39860-008

This document was generated on 05/12/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION