




Part Number : [731317003](#)

Product Description : 75 Ohms, BNC Vertical PCB Bulkhead Jack Receptacle, Panel Isolated, Black PBT Housing

Series Number : 73131

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[731317003_sd.pdf](#)

3D Models and Design Files

[731317003_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per ED/71/2019 (16 July 2019)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73131
Description	75 Ohms, BNC Vertical PCB Bulkhead Jack Receptacle, Panel Isolated, Black PBT Housing
Product Name	BNC
Style	PCB
Type	Miniature
UPC	800753685987

Electrical

Frequency	2 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	14.834/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	WAVE
Max-Temp	245