



Part Number : 731710700
Product Description : 75 Ohms, BNC Right-Angle, Low Profile, PCB Jack Receptacle
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[731710700_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	75 Ohms, BNC Right-Angle, Low Profile, PCB Jack Receptacle
Product Name	BNC
Style	PCB
Type	Miniature
UPC	800754027007

Electrical

Frequency	4 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	11.524/g
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Cycle	2

Max-Temp	260
----------	-----

This document was generated on Mar 01, 2025