



Part Number : 731375013
Product Description : BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, White PBT Housing, Height 13.20mm, Nut and Lockwasher included, Tin Plated Leads
Series Number : 73137
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[731375013_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73137
Description	BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, White PBT Housing, Height 13.20mm, Nut and Lockwasher included, Tin Plated Leads
Comments	13.20mm Profile
Product Name	BNC
Style	PCB
Type	Miniature
UPC	800753692060

Agency

CSA	LR19980
UL	E107635

Electrical

Frequency	2 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Flammability	94V-0
Gender	Jack
Keying to Mating Part	None
Net Weight	14.735/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole

PCB Thickness - Recommended	3.20mm
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	245