


DATASHEET

USB-A 2.0 Waterproof cable (Female to Male)

Item No. 3385885

Overview



Technical data

Rated current	1.5 A
Rated voltage	5 V
Nominal voltage	30 V
Protection level	IP67
Temperature range	-25 to 80 °C
Insertion and removal times	≥500
Cable length	0.5 m
Connection type	USB-A
Connection A	USB 2.0 connector A
Connection B	USB 2.0 socket A
Cable diameter	4.35 - 4.65 mm
Contact material	Copper alloy
Housing material	PVC

