



VELCRO USA INC.

95 Sundial Ave – Manchester, NH – 03103
Tel: (800) 225 0180 – Fax: (800) 835 2761
www.velcro.com

VELCRO® Brand EASY HANG

Category: Core
Family: Ties and Straps

Product Specification Sheet

Date (Dec 2019)

Product Description

VELCRO® Brand EASY HANG™ Storage Straps can help you maximize the space in your garage, basement or storage area by using the vertical space. Golf clubs, bikes, kayaks, hoses, extension cords, tools.... The possibilities are limitless.

Product Image



Product Options

Colors:	Black, (Green/Orange Medium only)
Lengths:	Extra Small 12in, Small 17 in, Medium 25in, Large 32in
Widths:	Extra Small 3/4in, Small and Medium 1in, Large 1 1/2in
Shapes:	Straps

Product Components

Hook:	Hook 88
Loop:	Loop 1000



VELCRO USA INC.

95 Sundial Ave – Manchester, NH – 03103
Tel: (800) 225 0180 – Fax: (800) 835 2761
www.velcro.com

Material Composition

Primary: Iron: Extra Small 46%, Small 56%, Medium 54%, Large 51%

Secondary: Zinc: Extra Small 37%, Small 32% Medium 31%, Large 28%

Technical Specifications

**Closure Peel
(PIW):** N/A

**Closure Shear
(PSI):** N/A

**Weight Rating
(PSI):** Extra Small 50 lbs. Small 100 lbs. Medium 200 lbs. Large 300 lbs.

Temp Range: 0° to 222°F

Packaging Image:



Packaging Information

Current Claims

- Maximize the space in your garage, basement, or storage area
- Strong hanging power - EASY HANG™ Straps Hold 50-300 pounds
- Simple, convenient, reusable
- Hang bikes, golf clubs, extension cords, tools, pool hoses & more
- Storage and organization has never been easier

Instructions

For maximum strength, ensure hook & loop surfaces overlap 100%



VELCRO USA INC.

95 Sundial Ave – Manchester, NH – 03103
Tel: (800) 225 0180 – Fax: (800) 835 2761
www.velcro.com

Flammability Resistance VELCRO® Brand EASY HANG™ Storage Straps is not fire retardant and should not be used where flammability resistance is a concern.

Water/Humidity resistance: VELCRO® Brand EASY HANG™ Storage Straps have low moisture regain, and are stable to dimensional changes due to temperature and humidity. VELCRO® Brand EASY HANG™ Storage Straps is not designed for underwater use. The closure will however, withstand incidental exposure to water.

Outdoor Use: VELCRO® Brand EASY HANG™ Storage Straps has good UV properties, but this system has not been tested for resistance to UV exposure. The system has been tested at normal operating temperatures and expected to perform satisfactorily in indoor and outdoor use.

Washing and Dry VELCRO® Brand EASY HANG™ Storage Straps should not be washed or dry cleaned.

Repositioning: VELCRO® Brand EASY HANG™ Storage Straps is designed to be removed and repositioned multiple times.

Shelf Life: VELCRO® Brand EASY HANG™ Storage Straps does not have a known shelf life.

Storage

General storage conditions: 65°F – 75°F (18C - 24C) with relative humidity of 40% – 65%. To extend shelf life, store in original packaging. Removal of release liner prior to application will shorten the product life cycle.

Product Use

The information, statements, and comments contained within this document are based on our experience and testing and are believed to be accurate. However, because there are many factors involved in specific applications that can impact end use and performance, product users should always test the product for its ability to meet the requirements of their specific use and method of application.

Limited Warranty

Velcro Industries* warrant that each product will substantially comply with its written specifications at the time of shipment. ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY DISCLAIMED. The product user is responsible for determining whether the product is fit and suitable for intended application. If the product does not meet specifications as warranted, we will, at our option, repair or replace the product, or credit or refund the purchase price. The foregoing constitutes the user's sole remedy and our sole obligation hereunder.

Limitation of Liability

To the maximum extent permitted under applicable law, Velcro industries' liability for any losses or damages relating to use of the product shall not exceed the purchase price for such product, regardless of whether such losses or damages are direct, indirect, special, incidental or

**VELCRO USA INC.**

95 Sundial Ave – Manchester, NH – 03103
Tel: (800) 225 0180 – Fax: (800) 835 2761
www.velcro.com

consequential, and regardless of the legal theory asserted, including, but not limited to, warranty, contract, negligence or strict liability.

USA
Velcro USA Inc.
Tel: (800) 225 0180
marketing@velcro.com
www.velcro.com

Spain
Velcro Europe S.A.
Tel: (34) 93 758 32 98
infovelcro@velcro.es
www.velcro.es

Italy
Velcro Italia, S.R.L.
Tel: (39) 039 62 70 01
commerciale@velcroitalia.it
www.velcro.it

China
Velcro Fastening Systems
Company Limited
Tel: (86) 512 8164 5888
www.velcro.com.cn

Canada
Velcro Canada Inc.
Tel: (800) 683 5276
canada@velcro.com
www.velcro.ca

Germany
Velcro GMBH
Tel: (49) 7141 991 19-0
info@velcro.de
www.velcro.de

UK
Velcro Limited
Tel: 44) 1606 73 88 06
uksales@velcro.com
www.velcro.co.uk

Hong Kong
Velcro Hong Kong Ltd.
Tel: (852) 2570 3698
www.velcro.com.hk

Mexico
Velcro de Mexico, S.A. de
C.V.
Tel (52) 55 5005 3300
salesmc@velcro.com
www.velcrodemexico.com

France
Velcro Industries France
S.A.
Tel : (33) 1 34 38 78 88
info@velcro.fr
www.velcro.fr

Australia
Velcro Australia Pty. Ltd.
Tel: (61) 3 9703 2466
sales@velcro.com.au
www.velcro.com.au

* Velcro Industries includes Velcro USA Inc. and all affiliates involved in development, manufacture or sale of the Products.