



Part Number : [1202530519](#)
Product Description : Contrinex Inductive Sensor, 4mm Diameter Smooth Housing, 1.5mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 38mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-623-04



Documents & Resources

Specifications
[1202530514-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, 4mm Diameter Smooth Housing, 1.5mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 38mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130069040

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 3000 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	38mm
Material - Housing	Stainless Steel
Material - Sensing Face	POM
Mounting Style	Embeddable
Net Weight	244.000/g
Operating Distance	1.5mm
Output	NO
Sensor Housing Size	4mm dia. (smooth)
Temperature Range - Operating	-25° to +70°C