



Part Number : [1202530378](#)
Product Description : Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Embeddable, NPN, NO, 4-pin M12 Connector, 60mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-621-M12



Documents & Resources

Specifications
[1202530374-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Embeddable, NPN, NO, 4-pin M12 Connector, 60mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130066230

Electrical

Output	NO
Polarity	NPN
Switching Frequency	≤ 2500 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	60mm
Material - Housing	Nickel Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Embeddable
Net Weight	648.000/g
Operating Distance	4mm
Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C