



Part Number : [1062250033](#)
Product Description : MPO Female-to-MPO
Female Trunk Cable Assembly, 9/125µm,
3.00mm, Singlemode, 12 Fiber, Plenum, OS2,
10.0m Length, Yellow
Series Number : 106225
Status : Active
Product Category : Fiber Optic Cable
Assemblies



Documents & Resources

Drawings
[1062250033_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106225
Description	MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 3.00mm, Singlemode, 12 Fiber, Plenum, OS2, 10.0m Length, Yellow
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Product Name	MPO
UPC	191128250443

Physical

Boot Type	Straight
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	9/125µm
Net Weight	99.361/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum