



Part Number : [1062250037](#)
Product Description : MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 3.80mm, Multimode, 12 Fiber, Plenum, OM3, 10.0m Length, Aqua
Series Number : 106225
Status : Active
Product Category : Fiber Optic Cable Assemblies



Documents & Resources

Drawings
[1062250037_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106225
Description	MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 3.80mm, Multimode, 12 Fiber, Plenum, OM3, 10.0m Length, Aqua
Connector to Connector	MPO-to-MPO
Mode	Multimode
Product Name	MPO
UPC	191128250481

Physical

Boot Type	Straight
Cable Length	10.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	169.383/g
Single Ended	No
Wire/Cable Type	12 Fiber OM3 Plenum