



Part Number : 2166201023
Product Description : 1.50mm Pitch, Pico-SPOX PCB Header, Single Row, Vertical, Surface Mount, Tin (Sn) Plating, Friction Lock, 4 Circuits, Tape and Reel, with Cap, Black
: 87437
: Active
Product Category : PCB Headers and Receptacles



874370463_sd.pdf

3D
874370463.dxf
874370463.pdf
874370463_stp.zip

874370000-AS-000.pdf
SPK-87437-001-001.pdf
874371001-PS-001.pdf
PS-87437-001-001.pdf

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Eu RoHS

- REACH SVHC

- Low-Halogen

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

RoHS

	PCB Headers and Receptacles
	87437
	1.50mm Pitch, Pico-SPOX PCB Header, Single Row, Vertical, Surface Mount, Tin (Sn) Plating, Friction Lock, 4 Circuits, Tape and Reel, with Cap, Black
	Signal, Wire-to-Board
	PCB Header
	Pico-SPOX
UPC	822350802994

CSA	LR19980
UL	E29179

	2.5A
-	250V AC (RMS)/DC

	4
	4

-	
() -	10
	94V-0
-	Brass
-	Tin
-	Tin
-	Nylon
	0.240/g
	1
	Embossed Tape on Reel
PCB	
PCB	
-	1.50mm
-	2.540µm
-	2.540µm
PCB	
	Pick and Place Cap
	Fully
	-55° to +105°C
	Surface Mount

/

Pico-SPOX Single Row Receptacle Housings	<u>87439</u>

This document was generated on Mar 03, 2025