



Part Number : [451410301](#)
Product Description : MultiCat-to-MultiCat
High-Power Off-the-Shelf (OTS) Cable
Assembly, Female, Single Row, 300.00mm
Length, 8 AWG, 3 Circuits, Key A, Black
Series Number : 45141
Status : Active
Product Category : Power and Signal Cable
Assemblies
Engineering Number : KAB2540L0.3V01



Documents & Resources

Drawings
[451410301_sd.pdf](#)

3D Models and Design Files
[451410301_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	45141
Description	MultiCat-to-MultiCat High-Power Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 300.00mm Length, 8 AWG, 3 Circuits, Key A, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MultiCat-to-MultiCat
Product Name	MultiCat
Type	Discrete Wire Assembly, High Reliability Assembly
UPC	191128291583

Electrical

Current - Maximum per Contact	40.0A
Voltage - Maximum	1000V AC

Physical

Cable Length	300.00mm
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus

Material - Plating Termination	Gold
Material - Resin	PEI
Net Weight	111.000/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	7.40mm
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10669
Wire Insulation Diameter	4.03mm-5.84mm
Wire Size (AWG)	8

Mates With / Use With

Mates with Part(s)

Description	Part Number
MultiCat High-Power Inline Plug Housing, 3 Circuits, Black, Key A	<u>2018400030</u>
MultiCat High-Power Vertical Header, 3 Circuits, Key A, Black	<u>2018421030</u>
MultiCat High-Power Right-Angle Header, 3 Circuits, Key A, Black	<u>2018431030</u>