




Part Number : [834249057](#)
Product Description : Commercial Micro-D,
CMD-to-CMD, 25 Circuits, Female - Female,
0.46m Length
Series Number : 83424
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[834249057_sd.pdf](#)
[PK-83422-001-001.pdf](#)

Specifications
[PS-83421-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	83424
Description	Commercial Micro-D, CMD-to-CMD, 25 Circuits, Female - Female, 0.46m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Commercial Micro-D-to-Commerci
Product Name	Commercial Micro-D
UPC	756054246405

Physical

Cable Length	0.46m
Circuits (Loaded)	25
Circuits (maximum)	25
Gender	Female-Female
Lock to Mating Part	None
Material - Plating Termination	Tin
Net Weight	46.430/g
Number of Rows	2
Packaging Type	Bag
Plating min - Mating	0.127µm
Plating min - Termination	1.270µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	N/A
Wire Insulation Diameter	.225mm (5.720") max.
Wire Size (AWG)	28
