

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88764-5900](#)
Status: **Active**
Overview: [High Definition Multimedia Interface \(HDMI\)* Products](#)
Description: 0.50mm Pitch HDMI*(F)-1.90mm Pitch P&D(M) Adapter



Series

image - Reference only

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	88768
Application	Wire-to-Board, Wire-to-Wire
Component Type	Adapter
Overview	High Definition Multimedia Interface (HDMI)* Products
Product Name	HDMI, MicroCross™P&D
Type	N/A
UPC	822348376292

Physical

Circuits (Loaded)	19
Circuits (maximum)	19
Color - Resin	Black
Durability (mating cycles max)	500
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin, Tin-Bismuth
Material - Resin	High Temperature Thermoplastic
Net Weight	40.000/g
Orientation	Horizontal
PCB Thickness - Recommended	1.00mm
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	1.016µm, 3.810µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Surface Mount, Through Hole

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	40V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-88764-006, SD-88764-590, SD-887645900
---------------	--

* High Definition Multimedia Interface and HDMI are trademarks of HDMI Licensing, LLC.

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

88768Series