




Part Number : [2177961103](#)
Product Description : KK 254-to-KK 254 Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 600.00mm Length, 10 Circuits, Natural
Series Number : 217796
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2177961103_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217796
Description	KK 254-to-KK 254 Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 600.00mm Length, 10 Circuits, Natural
Assembly Configuration	Dual Ended Connectors
Connector to Connector	KK 254-to-KK 254
Product Name	KK 254
Type	Discrete Wire Assembly
UPC	195842122970

Physical

Cable Length	600.00mm
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural (White)
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	28.880/g
Number of Rows	1
Pitch - Mating Interface	2.54mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Insulation Diameter	1.57mm max.
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Vertical Breakaway Headers with Friction Lock	<u>42375</u>
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	<u>42377</u>
KK 254 Right-Angle Breakaway Headers	<u>42376</u>
KK 254 Single Row Vertical Headers	<u>4030</u>
KK 254 Vertical Single Row Solid Headers	<u>6373</u>
KK 254 Vertical Single Row Headers	<u>6410</u>
KK 254 RPC Vertical Headers with Friction Lock	<u>171856</u>
KK 254 RPC Right-Angle Headers with Friction Lock	<u>171857</u>