



Part Number : [2183101021](#)
Product Description : Mini-Fit Sigma-to-Mini-Fit Sigma Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 150.00mm Length, 2 Circuits, Black
Series Number : 218310
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2183101021_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	218310
Description	Mini-Fit Sigma-to-Mini-Fit Sigma Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 150.00mm Length, 2 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Sigma Both Ends
Product Name	Mini-Fit Sigma
Type	Discrete Wire Assembly
UPC	195842330757

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V AC/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	8.767/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	4.20mm

Plating min - Mating	2.500µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Insulation Diameter	1.98-2.55mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Glow-Wire Capable, 2 Circuits	<u>1727621002</u>
Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Dual Row, Panel Mount, UL 94V-0, Glow-Wire Capable, 2 Circuits	<u>1727673002</u>
Mini-Fit Vertical Dual Row Headers	<u>172447</u>
Mini-Fit Jr. Right-Angle Dual Row Headers	<u>172448</u>
Mini-Fit 4.20mm Pitch Dual Row Right-Angle Headers	<u>35317</u>
Mini-Fit 4.20mm Pitch Dual Row Right-Angle Headers	<u>35318</u>
Mini-Fit Jr. Vertical Dual Row Headers	<u>43460</u>
Mini-Fit Jr. Right-Angle Dual Row Headers	<u>44130</u>
Mini-Fit Jr. Vertical, Dual Row, Reflow Solder Capable Headers	<u>46207</u>
Mini-Fit Jr. Right-Angle Dual Row Reflow Solder Capable Headers	<u>46991</u>
Mini-Fit Jr. Vertical Headers	<u>5566</u>
Mini-Fit Jr. Right-Angle Headers	<u>5569</u>
Mini-Fit Jr. Dual Row Headers	<u>87427</u>
