



Part Number : [2183231083](#)
Product Description : DuraClik ISL-to-Pigtail
Off-the-Shelf (OTS) Cable Assembly, 2.00mm
Pitch, Single Row, 600.00mm Length, 8
Circuits, White
Series Number : 218323
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2183231083_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	218323
Description	DuraClik ISL-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 600.00mm Length, 8 Circuits, White
Application	Automotive, Signal, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	DuraClik ISL-to-Pigtail
Product Name	DuraClik
Type	Discrete Wire Assembly
UPC	195842351912

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Length	600.00mm
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	White
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PBT
Net Weight	24.400/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag

Pitch - Mating Interface	2.00mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	FLRY-A
Wire Insulation Diameter	1.30mm
Wire Size mm ²	0.35

Mates With / Use With

Mates with Part(s)

Description	Part Number
DuraClik Right-Angle Single Row Headers	<u>502352</u>
DuraClik Vertical Single Row Headers	<u>560020</u>