




Part Number : [2076025002](#)
Product Description : Grounding Jumper
without Insulation, Flat-to-Flat, 24x5/30 Braid
Type, 305.00mm Length
Series Number : 207602
Status : Active
Product Category : Busbars



Documents & Resources

Drawings
[2076025002_sd.pdf](#)

3D Models and Design Files
[2076025002_stp.zip](#)

Specifications
[2076025000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Busbars
Series	207602
Description	Grounding Jumper without Insulation, Flat-to-Flat, 24x5/30 Braid Type, 305.00mm Length
Keyword	grounding jumpers, grounding strap, grounding straps, ground strap, ground straps, busbar
Product Name	Grounding Jumper
UPC	191128896993

Electrical

Current - Maximum per Contact	53.0A
-------------------------------	-------

Physical

Approximate AWG Equivalent	10
Approximate Circular Mils	12060
Braid Type	24x5/30
Insulation	None
Length	305.00mm
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Orientation	Flat-to-Flat
Packaging Type	Carton