




Part Number : [923150852](#)
Product Description : Picoflex PF-50 IDT-to-Picoflex PF-50 IDT Cable Assembly, 0.52m Length, Tin (Sn) Plating, 8 Circuits
Series Number : 92315
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[923150852_sd.pdf](#)

3D Models and Design Files
[923150852_stp.zip](#)

Specifications
[908140000-AS-000.pdf](#)
[PS-99020-0011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	92315
Description	Picoflex PF-50 IDT-to-Picoflex PF-50 IDT Cable Assembly, 0.52m Length, Tin (Sn) Plating, 8 Circuits
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Picoflex IDT-to-IDT
Product Name	Picoflex
UPC	822348679720

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

Physical

Cable Length	0.52m
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Gender	Female-Female
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	8.092/g
Number of Rows	2

Packaging Type	Bag
Pitch - Mating Interface	1.27mm
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Single Ended	No
Termination Interface Style	IDT or Pierce
Waterproof / Dustproof	No
Wire/Cable Type	PVC, Ribbon Cable
Wire Insulation Diameter	N/A
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Picoflex PF-50 Vertical Low Profile Headers	<u>90325</u>
Picoflex PF-50 Vertical Low Profile Headers	<u>90779</u>
Picoflex PF-50 Vertical Surface Mount Headers	<u>90814</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for Connectors	<u>621006000</u>