


10		9	8	7	6	5	4	3	2	106012
P/N OF CONNECTOR	D (μm)	MATERIAL of FERRULE	COLOR of BOOT	CABLE TYPE						
106012-0300	127	Zr PLUS	BLACK	MULTIMODE						
106012-0310*										
106012-3300	128	Zr		SINGLE MODE						
106012-5300	126									
106012-5310*										
106012-5360				BLACK (SOFT)						



NOTES:

* P/N 106012-0310 AND P/N 106012-5310 ARE BULK PACKED IN QUANTITIES OF 100 PCS.

ENTER DESCRIPTION EC NO: MF2017-0132 DRAWN: HANUMAPPARE 2016/11/03 CHKD: IGUMIN APPR: IGUMIN		DESCRIPTION 2016/11/16	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 	
C		REV		mm		INCH		DRAWN BY DATE RPACIFICI 2005/12/22		TITLE ST CONNECTOR (METAL NUT, CRIMP VERSION)	
				4 PLACES ± --- ± ---		3 PLACES ± --- ± ---		CHECKED BY DATE			
				3 PLACES ± --- ± ---		2 PLACES ± --- ± ---		APPROVED BY DATE		molex	
				2 PLACES ± --- ± ---		1 PLACE ± --- ± ---					
				1 PLACE ± --- ± ---		0 PLACE ± ±					
ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-106012-X3X0		1 OF 1					
SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									