




Part Number : [2181120701](#)
Product Description : PicoBlade Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, 7 Circuits, Natural
Series Number : 218112
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2181120701_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	218112
Description	PicoBlade Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, 7 Circuits, Natural
Application	Signal, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	PicoBlade-to-Pigtail
Product Name	PicoBlade
Type	Discrete Wire Assembly
UPC	195842250741

Physical

Cable Length	150.00mm
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Natural
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.596/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	Yes

Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Insulation Diameter	0.50-1.00mm
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Vertical, Single Row, Through Hole Headers	<u>53047</u>
PicoBlade Right-Angle, Single Row, Through Hole Headers	<u>53048</u>
PicoBlade Right-Angle, Single Row, Surface Mount Headers	<u>53261</u>
PicoBlade Vertical, Single Row, Surface Mount Headers	<u>53398</u>
PicoBlade Single Row Plug Housings	<u>51047</u>