



Part Number : 731160076
Product Description : MCRF-to-Pigtail, 0.81mm Cable Diameter, Length 230.13mm, H18, 50 Ohms, One Piece Per Bag
Series Number : 73116
Status : New Business Not Supported
Product Category : RF Cable Assemblies



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/61/2018 (27 June 2018)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
--------	----------------------------

Category	RF Cable Assemblies
Series	73116
Description	MCRF-to-Pigtail, 0.81mm Cable Diameter, Length 230.13mm, H18, 50 Ohms, One Piece Per Bag
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Product Name	MCRF
Type	RF Cable Assembly
UPC	884982813632

Electrical

Impedance	50Ω
-----------	-----

Physical

Cable Length	230.13mm
Gender	Plug/Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.800/g
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	0.81mm, Coaxial

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----