



Part Number: 78308-2230
0.6MM DDR2 SODIMM STD 5.2H .76AuLF200Ckt

Image not available

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	78308
Category:	Molex Parts

Series image - Reference only

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Not Reviewed

Part Detail

General	
Status	
Category	
Series	
Solder Process Data	
Duration at Max. Process Temperature (seconds)	20
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	2
Process Temperature max. C	260
Material Info	
UPC	883906030728

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)