


MATERIALS AND FINISHES

SMA PLUG: SEE SD-73251-489

CABLE: TEMP-FLEX 1000540008

SHRINK TUBE: VERSAFIT OR EQUIVALENT

LABEL : BRADY PERMASLEEVE



89762-1373	19.685±.492	500.00±12.5	1.10
89762-1372	120.000±2.00	3048.00±50.80	7.00
89762-1371	12.00±.200	304.80±5.08	0.70
89762-1370	6.000±.150	152.40±3.81	0.40
PART NO.	IN	MM	INSERTION LOSS MAX
	DIM A		TO 26 GHZ (dB)

MAX VSWR 1.35 TO 26 GHZ

CHG: CHANGED CABLE
TYPE TO 1000540008
(PFA 141 AC)

EC NO: URF2017-0259
DRWN:PSWAM102
CHKD:BBB
APPR:AROBERTSON

2016/12/26
2016/12/26
2017/01/16

DESCRIPTION
REV

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .010
2 PLACES ± 0.25 ± ---
1 PLACE ± --- ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
JLEE02 2013/03/27
CHECKED BY DATE
SSS 2013/03/27
APPROVED BY DATE
JWIENER 2013/08/29
MATERIAL NO.
SEE TABLE
SIZE C

SCALE
DESIGN UNITS
METRIC
TITLE
SMA PLUG ST X2 ON
TF 1000540008 CABLE
EWR-10382-A, CA-SMA/SMA
molex MOLEX INCORPORATED
DOCUMENT NO.
SD-89762-137
SHEET NO.
1 OF 1