

Part Number: 78308-1130

0.6MM DDR SODIMM STD 5.2H .76AuLF 200Ckt

Status: OBSOLETE

Replacement: Contact Molex

Series: 78308

Category: Molex Parts

Go to [Part Detail](#)

Image not available

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Specifications & Other Documents:

Documents not available online

Sales Drawings, 3D Models, and Brochures

Documents not available online

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant

China RoHS: 

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Low-Halogen

Part Detail

COLLAPSE ALL

General

Status

Category

Series

Physical

Flammability

94V-0

Agency Certification

CSA

LR19980

UL

E29179

Solder Process Data

Duration at Max. Process Temperature (seconds)

20

Lead-free Process Capability

Reflow Capable (SMT only)

Max. Cycles at Max. Process Temperature

2

Process Temperature max. C

260

Material Info